

D46 GC Ferrules & Sealing Rings

SGE Graphitized Vespel Ferrules 350°C-GVF - the Standard for GC/MS


These Vespel ferrules contain 15% graphite and are ideal for glass and fused silica capillary columns. Because these ferrules are harder, they do not distort and flow as much as other types and are ideal for butt type connections where the flowpath might need to be disconnected.

For connecting fused silica tubing we recommend a ferrule size slightly larger than the O.D. of the column to be selected.

No-hole ferrules are available and can be drilled to suit a particular application or to seal off a fitting.

Two-hole ferrules can be utilized to split the column effluent between two detectors or one detector and a collector. The two-hole ferrule can also be used for inlet splitting between two fused silica columns.

Three-hole ferrules are also available for multiple splitting. To suit the SGE range of mini unions, special small graphitized vespel ferrules are available.



Part No.	Order code	Fitting Size	Hole Size	W (mm)	L (mm)	Price / Pk of 10
072661	GVF16/000	1/16"	no hole	3.2	3.7	
0726632	GVF16/002	1/16"	0.2mm	3.2	3.7	
072659	GVF16/003*	1/16"	0.3mm	3.2	3.7	
072663	GVF16/004	1/16"	0.4mm	3.2	3.7	
072654	GVF16/005	1/16"	0.5mm	3.2	3.7	
072655	GVF16/008	1/16"	0.8mm	3.2	3.7	
072658	GVF16/009	1/16"	0.9mm	3.2	3.7	
072656	GVF16/010	1/16"	1.0mm	3.2	3.7	
072657	GVF16/16	1/16"	1/16"	3.2	3.7	
072660	GVF16/(2)-003	1/16" (2 hole)	2 x 0.3mm	3.2	3.7	
072662	GVF16/(2)-004*	1/16" (2 hole)	2 x 0.4mm	3.2	3.7	
072664	GVF16/(2)-005	1/16" (2 hole)	2 x 0.5mm	3.2	3.7	
0726640	GVF16/(2)-005-003	1/16" (2 hole)	0.5 & 0.3mm	3.2	3.7	
0726641	GVF16/(2)-004-003	1/16" (2 hole)	0.4 & 0.3mm	3.2	3.7	
0726642	GVF16/(2)-005-004	1/16" (2 hole)	0.5 & 0.4mm	3.2	3.7	
072665	GVF16/(3)-004*	1/16" (3 hole)	3 x 0.4mm	3.2	3.7	
072670	GVF8/000	1/8"	no hole	6.4	7.4	
0726701	GVF8/16	1/8"	1/16"	6.4	7.4	
072669	GVF8/8	1/8"	1/8"	6.4	7.4	
0726703	GVF8/04	1/8"	0.4mm	6.4	7.4	
0726702	GVF8/05	1/8"	0.5mm	6.4	7.4	
072671	GVF8/08	1/8"	0.8mm	6.4	7.4	
0726700	GVF8/2.4	1/8"	2.4mm	6.4	7.4	
072674	GVF8(2)-008	1/8" (2 hole)	2 x 0.8mm	6.4	7.4	
072666	GVF4/000	1/4"	no hole	9.5	7.4	
0726660	GVF4/005**	1/4"	0.5mm	9.5	7.4	
072673	GVF4/16	1/4"	1/16"	9.5	7.4	
072668	GVF4/8	1/4"	1/8"	9.5	7.4	
072667	GVF4/4	1/4"	1/4"	9.5	7.4	
0726673	GVF4/60	1/4"	6.0mm	9.5	7.4	
072694	MGVF/000	For SGE MVSU mini-union	no hole			
072695	MGVF/003*	For SGE MVSU mini-union	0.3mm			
072696	MGVF/004	For SGE MVSU mini-union	0.4mm			
072697	MGVF/005	For SGE MVSU mini-union	0.5mm			
072698	MGVF/008	For SGE MVSU mini-union	0.8mm			
072693	MGVF/16	For SGE MVSU mini-union	1/16"			

*Will seal down on to .17mm O.D. tubing

**Ion trap detector ferrule for PE, Thermo Finnigan and Varian

Graphitized Vespel Sealing Rings 350°C (SGE Fittings Only) - VSR

Specifically shaped for SGE 1/16", 1/8" and 1/4" stainless steel union they are supplied as standard with a number of SGE products. Back ferrules are not required.

Part No.	Order code	Fitting Size	Hole Size	Price / Pk of 10
0726520	GSR16/16(graphite)	1/16"	1/16"	
072653	VSR16/16	1/16"	1/16"	
072652	VSR8/8	1/8"	1/8"	
072651	VSR4/4	1/4"	1/4"	
0726003	GSR 4/4(graphite)	1/4"	1/4"	