


E34 SIS™ HPLC Fittings

SIS Double-Ferrule Fittings


Use these fittings for 1/16" tubing and any 10-32 female connection. The double-sided ferrule grips twice for the strongest fingertight connections up to 420 bar (6000 psi).



Part Number	Description
E300	Hex nut standard
E310	Hex nut long
E320	Handtight nut PEEK
E330	Stainless handtight nut
E905	PEEK double ferrule

SIS Universal Fingertight Fitting

Connects with any male or female 10-32 fitting. Fingertight connection rated to 350 bar (5000 psi). Use a wrench to achieve a 560 bar (8000 psi) connection.



Part Number	Description
E340	Universal Fingertight Nut
E905	PEEK double ferrule

SIS One-Piece Fingertight Fitting

Ferrule and fitting in one! Works with any 10-32 female port and both metal and polymeric 1/16" tubing. Rated to 420 bar (6000 psi). These fittings are available in six colors for easy solvent/mobile phase identification.



Part Number	Description
E351	One piece fitting Natural molded PEEK
E352	Black
E353	Red
E354	Yellow
E355	Blue
E356	Green
E350	Natural machined PEEK

SIS Stainless Steel Nuts and Ferrules

Machined from high-quality 316L stainless steel. Nuts with 10-32 threads are available in three different lengths.



Part No.	Description	Qty/Pk
E400	1/16" nut 10-32 threads	5
E401	long 1/16" nut 10-32 threads	5
E402	extra long 1/16" nut 10-32 threads	5
E906	1/16" stainless steel ferrule	10
E405	1/16" plug 10-32 threads	2
E410	1/8" plug 5/16"-24 threads	2
E415	1/8" nut 5/16"-24 threads	5
E907	1/8" stainless steel ferrule	5

► **Teck Tip** Use different nut lengths on adjacent valve ports for easier assembly/disassembly.