

F4 Ionization Gauge Tubes

PTFE and Glass Filled PTFE Ferrules for Ion Gauge Tubes

These 3/4" ferrules are used to install Ion Gauge Tubes. They are available in two compositions, PTFE and Glass filled PTFE. PTFE ferrules are for standard use under most operating conditions. Glass filled PTFE exhibits less flow at elevated temperatures and therefore have a longer life and greater leak resistance. Usable to 250°C.



Part No.	Description	Price
T-12131	3/4" PTFE Ferrule Pkg. of 10	
GFT-1213	3/4" Glass Filled PTFE Ferrule Pkg. of 10	

Ion Gauge Adapter Flange


3/4" O-Ring connector to 2 3/4" Conflat flange. Use this to adapt ion gauge tubes to a 2 3/4" Conflat flange. Other sizes and configurations are available on special request.



Part No.	Description	Price
FC75	Ion gauge adapter flange	

Mini Ion Gauge Tube

The Mini Ion Gauge Tubes are available from S.I.S.™. The controller electronics and cable are available if you did not buy this device with your instrument and now wish to upgrade.



Part No.	Description	Price ea.
342003	Agilent 5972/5973/5975, LTQ, LCQ, DSQ Ion Gauge Tube	
342022	Agilent 5972/5973/5975, LTQ, LCQ, DSQ Ion Gauge Controller	
342023	Agilent 5972/5973/5975, LTQ, LCQ, DSQ Ion Gauge Cable	